



# Ethernet Series Accessories

## 4 & 8 Conductor Ethernet Series Accessory Cables



100' Cables | Raw Cable Spools | CAT5e | Twisted Pairs

Ethernet Series L

# of Conductors	Color Code	Wire AWG Rating	Features	DC Resistance	Continuous Flex	Part Number	
						100' Cable	Spool
4	White/Orange White/Green Orange Green	24 AWG Stranded 150V	Teal PVC AWM CMX/CMR -20°C to +80°C 6.1mm OD (0.24" OD)	≤ 89 Ω/Km	No	MDE45-4CBL-C	60C0001-*
			Teal PVC AWM CMX/CMR With Foil/Braided Shield -20°C to +80°C 6.6mm OD (0.26" OD)	≤ 89 Ω/Km	No	MDE45M-4CBL-C	60CS001-*
			Teal PUR AWM -40°C to +80°C 5.6mm OD (0.22" OD)	≤ 91 Ω/Km	Yes	MDE45P-4CBL-C	60CP001-*
			Teal PUR AWM With Foil/Braided Shield -40°C to +80°C 6.4mm OD (0.25" OD)	≤ 91 Ω/Km	Yes	MDE45PB-4CBL-C	60CSP01-*
			Teal TPE AWM CMX/CMR With Foil/Braided Shield -40°C to +80°C 6.6mm OD (0.26" OD)	≤ 140 Ω/Km	Yes	MDE45WB-4CBL-C	60CSW01-*
			Red TPE AWM CMX/CMR With Foil/Braided Shield -40°C to +80°C 6.6mm OD (0.26" OD)	≤ 140 Ω/Km	Yes	MDE45WB-4CBL-C-RD	60CSWR1-*
8	White/Blue White/Brown Brown Orange White/Green White/Orange Blue Green	24 AWG Stranded 60V	Teal PVC AWM CMX/CMR -20°C to +80°C 6.4mm OD (0.25" OD)	≤ 89 Ω/Km	No	MDE45-8CBL-C	60G0001-*
			Teal PVC AWM With Foil/Braided Shield -20°C to +80°C 7.6mm OD (0.29" OD)	≤ 89 Ω/Km	No	MDE45B-8CBL-C	60GS001-*
			Teal PUR AWM -40°C to +80°C 6.3mm OD (0.24" OD)	≤ 91 Ω/Km	Yes	MDE45P-8CBL-C	60GP001-*
		26 AWG Stranded 60V	Teal PUR CMX With Foil/Braided Shield -40°C to +75°C 6.3mm OD (0.24" OD)	≤ 140 Ω/Km	Yes	MDE45PB-8CBL-C	60GSP02-*
		24 AWG Stranded 60V	Teal TPE AWM CMX/CMR With Foil/Braided Shield -40°C to +80°C 7.6mm OD (0.30" OD)	≤ 86 Ω/Km	Yes	MDE45WB-8CBL-C	60GSW01-*

\* Standard raw spool lengths are 0250, 0500, 0750 & 1000 feet. Consult factory for other lengths.

All testing is conducted off the reel and without connectors attached.  
Cable Construction subject to change without notice.