



MIL-SPEC Series Field Wireable Plugs



2 & 3 Conductor 5015 Industrial Equiv. Field Wireable Plugs, 16-18AWG



Field Wireable Plugs | Size 10SL | 600 Volt, 13 amps MAX | IP67 Rating



F
MIL-SPEC

# of Poles	Male Faceview	Rating	Wire AWG	Cable O.D. Range	Male Plugs	Female Plugs
2	 <p>10SL-2 0.6250"-24NEF</p>	600V Max 13A Max	16-18 AWG	3-9 mm	MS10SL-2MP-FW16-SC	MS10SL-2FP-FW16-SC
3	 <p>10SL-3 0.6250"-24NEF</p>	600V Max 13A Max	16-18 AWG	3-9 mm	MS10SL-3MP-FW16-SC	MS10SL-3FP-FW16-SC

Voltage and Amperage ratings are cable dependent and are based on 600V 16AWG Cable.

Termination made by solder cup.

Specifications:

- Body: Nickel Plated Brass
- Contacts: Copper Alloy with Silver Plating
- Cable Seal: CR/NBR & TPE
- Coupling Nut: Nickel Plated Brass
- Insert: PBT
- Connections: Solder Cup Terminals
- Temperature: -40 °C to +105°C (-40°F to +194°F)

