



MIL-SPEC Series Field Wireable Plugs

4, 5, 6 & 7 Conductor 5015 Industrial Equiv. Field Wireable Plugs, 16-18AWG



Field Wireable Plugs | Size 14S | 600 Volt, 10/8/5 amps MAX | IP67 Rating



F
MIL-SPEC

# of Poles	Male Faceview	Rating	Wire AWG	Cable O.D. Range	Male Plugs	Female Plugs
4	<p>14S-4 0.8750"-20UNEF</p>	600V Max 10A Max	16-18 AWG	5-13 mm	MS14S-4MP-FW20-SC	MS14S-4FP-FW20-SC
5	<p>14S-5 0.8750"-20UNEF</p>	600V Max 8A Max	16-18 AWG	5-13 mm	MS14S-5MP-FW20-SC	MS14S-5FP-FW20-SC
6	<p>14S-6 0.8750"-20UNEF</p>	600V Max 8A Max	16-18 AWG	5-13 mm	MS14S-6MP-FW20-SC	MS14S-6FP-FW20-SC
7	<p>14S-7 0.8750"-20UNEF</p>	600V Max 5A Max	16-18 AWG	5-13 mm	MS14S-7MP-FW20-SC	MS14S-7FP-FW20-SC

Voltage and Amperage ratings are cable dependent and are based on 600V 16AWG Cable.

Termination made by solder cup.

Specifications:

- Body: Nickel Plated Brass
- Contacts: Copper Alloy with Silver Plating
- Cable Seal: CR/NBR & TPE
- Coupling Nut: Nickel Plated Brass
- Insert: PBT
- Connections: Solder Cup Terminals
- Temperature: -40 °C to +105°C (-40°F to +194°F)

