



7/8" JIN Junction Blocks

8 Port, 4 Pin/3 Wire JIN Junction blocks



Standard Wiring | MIN Receptacle & Cable | IP67 Protection Rating

Trunk Style	Trunk Connection	Part Number	Circuit
	MIN Size III 10 Pole Male Receptacle	JIN-840-010-M000	
	Yellow PVC AWM 2661 10 x 18 AWG 300V 10.2mm OD	JIN-840-010-C**	

JIN Junction Blocks

P

Cables for JIN-840-010-M000				Female Receptacle	
Single Ended Home Run Cable		Double Ended Home Run Cable			
MIN-10FPX-*	Page C-3	MIN-10MFPX-*	Page C-8	MIN-10FR-1-18	Page C-15

* Length in feet. Standard Cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard Cable lengths are 2, 5 & 10 meters. Consult factory for other lengths.

Standard housing is aluminum alloy, for stainless steel housing add a "SS" right after JIN. (e.g. JIN-840-010-M000 becomes JINSS-840-010-M000)

Specifications:

- Housing: Black Epoxy Coated Die Cast Aluminum Alloy
- Connectors: Anodized Aluminum, Oil Resistant PVC Contact Carrier
- Cable Gland: Nickel Plated Brass, Polyamide and TPE Inserts
- Contacts: Copper Alloy with Gold Plating
- Temperature: -30 °C to +80 °C (-22°F to +176°F)
- Amperage: 4A per Port, 8A per Unit