



Panel Interface Connectors

Other Popular Models



Duplex Versions | Standard Metal Housing | NEMA/UL 4, 4X, 12 | IP66 Rating

| Part Number | Description |
|----------------------------|---|
| DP-2-32 | 2 x Duplex Receptacles, Size 32 Housing |
| DP-2DB9-32 | Duplex Receptacle, 2 x 9 Pin D-Sub, Size 32 Housing |
| DP-2RJ45-32 | Duplex Receptacle, 2 x RJ45, Size 32 Housing |
| DP-2RJ45-6R-32 | Duplex Receptacle, 2 x RJ45, 6 AMP Reset, Size 32 Housing |
| DP-2RJ45-R-P32 | Duplex Receptacle, 2 x RJ45, 3 AMP Reset, Size 32 Surface Mount Housing |
| DP-2USB-*-2RJ45-32 | Duplex Receptacle, 2 x USB Form A Cables, 2 x RJ45, Size 32 Housing |
| DP-DB15-R-32 | Duplex Receptacle, 15 Pin D-Sub, 3 AMP Reset, Size 32 Housing |
| DP-DB15-RJ45-R-32 | Duplex Receptacle, 15 Pin D-Sub, RJ45, 3 AMP Reset, Size 32 Housing |
| DP-DB25-PC8-R-32 | Duplex Receptacle, 25 pin D-Sub connected to 8 Pin Pluggable Screw Terminal Block, 3 AMP Reset, Size 32 Housing |
| DP-DB25-R-32 | Duplex Receptacle, 25 Pin D-Sub, 3 AMP Reset, Size 32 Housing |
| DP-DB9-8M-R-32 | Duplex Receptacle, 9 Pin D-Sub, 8 Pin Mini-DIN, 3 AMP Reset, Size 32 Housing |
| DP-DB9-DB15-R-32 | Duplex Receptacle, 9 Pin D-Sub, 15 Pin D-Sub, 3 AMP Reset, Size 32 Housing |
| DP-DB9F-R-32 | Duplex Receptacle, 9 pin D-Sub Female Exterior/Female Interior, 3 AMP Reset, Size 32 Housing |
| DP-DB9F-RJ45S-R-32 | Duplex receptacle, 9 pin D-Sub Female Exterior/Female Interior, Shielded RJ45, 3 AMP reset, Size 32 housing |
| DP-DB9M-RJ45-R-32 | Duplex receptacle, 9 pin D-Sub Male Exterior/Male Interior, RJ45, 3 AMP reset, Size 32 housing |
| DP-DB9-NR-32 | Duplex Receptacle, 9 pin D-Sub, No Reset, Size 32 Housing |
| DP-DB9-PC9-R-32 | Duplex Receptacle, 9 Pin D-Sub Female to a Discrete Wire Pluggable Screw Terminal Block, 3 AMP Reset, Size 32 Housing |
| DP-DB9-RJ45-5R-32 | Duplex Receptacle, 9 Pin D-Sub, RJ45, 5 AMP Reset, Size 32 Housing |
| DP-DB9-RJ45-NR-32 | Duplex Receptacle, 9 Pin D-Sub, RJ45, No Reset, Size 32 Housing |
| DP-DDB15-6M2-RJ45-USB-R-48 | Duplex Receptacle, Hi-Density 15 Pin D-Sub, 2x6 Pin Mini-DIN, RJ45, 2xUSB Form A, 3 AMP Reset, Size 48 Housing |
| DP-DDB15F-RJ45-32 | Duplex Receptacle, Hi-Density 15 Pin D-Sub Male Exterior/Interior, RJ45, Size 32 Housing |
| DP-DDB15-RJ45-4USB-*-48LS | Duplex Receptacle, Hi-Density 15 Pin D-Sub, RJ45, 4 x USB Form A Cables, Size 48 Housing |
| DP-DDB15-RJ45-R-32 | Duplex Receptacle, Hi-Density 15 Pin D-Sub, RJ45, 3 AMP Reset, Size 32 Housing |
| DP-DN-R-32 | Duplex Receptacle, DeviceNet Open Style Connector, 3 AMP Reset, Size 32 Housing |
| DP-EV1-48LS | Duplex Receptacle, 9 pin D-Sub, Hi-Density 15 pin D-Sub, 2x6 Pin Mini-DIN Female, 25 pin D-Sub, RJ11, Size 48 Housing |
| DP-MDB9-R-32 | Duplex Receptacle, 9 Pin D-Sub Male Exterior/Female Interior, 3 AMP Reset, Size 32 Housing |
| DP-RJ11-R-32 | Duplex receptacle, RJ11, 3 AMP reset, Size 32 housing |
| DP-RJ45-10R-32 | Duplex Receptacle, RJ45, 10 AMP Reset, Size 32 Housing |
| DP-RJ45-15R-32 | Duplex Receptacle, RJ45, 15 AMP Reset, Size 32 Housing |
| DP-RJ45-2USB-AFAF-P32 | Duplex Receptacle, RJ45, 2 x USB Form A Female to Female, Size 32 Surface Mount Housing |
| DP-RJ45-2USB-AFAF-R-32 | Duplex Receptacle, RJ45, 2 x USB Form A Female to Female, 3 AMP Reset, Size 32 Surface Mount Housing |
| DP-RJ45-2USB-AFBF-R-32 | Duplex Receptacle, RJ45, 2 x USB Form A Female to Form B Female, 3 AMP Reset, Size 32 Surface Mount Housing |
| DP-RJ45-6M-32 | Duplex Receptacle, RJ45, 6 Pin Mini-DIN Female, Size 32 Housing |
| DP-RJ45-8M-R-32 | Duplex Receptacle, RJ45, 8 Pin Mini-DIN Female, 3 AMP Reset, Size 32 Housing |

* Length in feet. Standard cable lengths are 3,6 & 10 feet. Consult factory for other lengths.