



# Panel Interface Connectors

Popular PIC Models



Low Profile LP2 & LP3 Housing | NEMA/UL 4, 4X, 12 | IP66 Rating

Part Number	Description	Faceview	Part Number	Description	Faceview
LP2-DP1-2DB9-RJ45-R	Single Outlet 2 x 9 Pin D-Subs RJ45 3 AMP Reset LP2 Housing		LP2-GF-RJ45S	GFCI Receptacle Shielded RJ45 LP2 Housing	
LP2-DP-3USB-AFAF	Duplex Receptacle 3 x USB A Female to Male Connector LP2 Housing		LP2-GF-RJ45-USB-AFAF	GFCI Receptacle RJ45 USB Form B Female to Form A Female LP2 Housing	
LP2-DP-RJ45-2USB-AFAF	Duplex Receptacle 2xUSB A Connections RJ45 LP2 Housing		LP2-GF-RJ45-USB-BFAF	GFCI Receptacle RJ45 USB Female Form B to Female Form A LP2 Housing	
LP2-DP-USB-*	Duplex Receptacle USB Form A Cable LP2 Housing		LP3-DP-2RJ45-R	Duplex Receptacle 2- RJ45 3 AMP Reset LP3 Housing	
LP2-GF-2DB9-RJ45	GFCI Receptacle 2 x 9 Pin D-Sub RJ45 LP2 Housing		LP3-DP-DB9F-RJ45S-R	Duplex Receptacle 9 pin D-Sub Female Shielded RJ45 LP3 Housing	
LP2-GF-2RJ45	GFCI Receptacle 2 x RJ45 LP2 Housing		LP3-DP-DB9-PC9-RJ45-R	Duplex Receptacle 9 Pin D-Sub to Terminal Block RJ45 3 AMP Reset LP3 Housing	
LP2-GF-2RJ45-USB-BFAF	GFCI Receptacle 2 x RJ45 USB Form B Female to Form A Female LP2 Housing		LP3-DP-DB9-RJ45-R	Duplex Receptacle 9 Pin D-Sub RJ45 3 AMP Reset LP3 Housing	
LP2-GF-RJ45	GFCI Receptacle RJ45 LP2 Housing		LP3-DP-R	Duplex Receptacle 3 AMP Reset LP3 Housing	
LP2-GF-RJ45-2USB-AFAF	GFCI Receptacle 2xUSB A connections RJ45 LP2 Housing		LP3-DP-RJ11-RJ45-R	Duplex Receptacle RJ11 RJ45 3 AMP Housing LP3 Housing	

\* Length in feet. Standard cable lengths are 3,6 & 10 feet. Consult factory for other lengths.

Panel Interface Connectors

V