



Panel Interface Connectors

Popular PIC Models



Low Profile LP3 Housing | NEMA/UL 4, 4X, 12 | IP66 Rating

| Part Number | Description | Faceview | Part Number | Description | Faceview |
|------------------------|---|----------|---------------------|--|----------|
| LP3-DP-RJ45-R | Duplex Receptacle RJ45 3 AMP Reset LP3 Housing | | LP3-GF-R | GFCI Receptacle 3 AMP Reset LP3 Housing | |
| LP3-DP-RJ45-USB-BFAF-R | Duplex Receptacle RJ45 USB Female Form B to Female Form A 3 AMP Reset LP3 Housing | | LP3-GF-RJ45 | GFCI Receptacle RJ45 LP3 Housing | |
| LP3-GF-15R | GFCI Receptacle 15 AMP Reset LP3 Housing | | LP3-GF-RJ45-15R | GFCI Receptacle RJ45 15 AMP Reset LP3 Housing | |
| LP3-GF-2RJ45-R | GFCI Receptacle 2 x RJ45 3 AMP Reset LP3 Housing | | LP3-GF-RJ45-R | GFCI Receptacle RJ45 3 AMP Reset LP3 Housing | |
| LP3-GF-2USB-AFAF-R | GFCI Receptacle 2xUSB A connections 3 AMP Reset LP3 Housing | | LP3-GF-RJ45S | GFCI Receptacle Shielded RJ45 LP3 Housing | |
| LP3-GF-DB15-R | GFCI Receptacle 15 Pin D-Sub 3 AMP Reset LP3 Housing | | LP3-GF-RJ45S-R | GFCI Receptacle Shielded RJ45 3 AMP Reset LP3 Housing | |
| LP3-GF-DB9F-RJ45-R | GFCI Receptacle 9 pin D-Sub Female Exterior/Female Interior RJ45 3 AMP Reset LP3 Housing | | LP3-GF-RJ45-USB-*-R | GFCI Receptacle RJ45 USB Form A Cables 3 AMP Reset LP3 Housing | |
| LP3-GF-DB9M-RJ45-R | GFCI Receptacle 9 Pin D-Sub Male Exterior/Male Interior RJ45 3 AMP Reset LP3 Housing | | LP3-GF-USB-AFAF-R | GFCI Receptacle USB Form A Female to Form A Female 3 AMP Reset LP3 Housing | |
| LP3-GF-DB9-RJ45-R | GFCI Receptacle 9 Pin D-Sub RJ45 3 AMP Reset LP3 Housing | | LP3-GF-USB-BFAF-R | GFCI Receptacle USB Form B Female to Form A Female 3 AMP Reset LP3 Housing | |

* Length in feet. Standard cable lengths are 3,6 & 10 feet. Consult factory for other lengths.