



DeviceNet Series Terminating Plugs

5 Conductor DeviceNet Series MIN & MDC Terminating Plugs



Terminating Plugs | IP67 Rating

Wiring: Pin 4 to pin 5 with 1/4 watt 121 Ohm 1% resistor

MIN Terminating Plugs			
# of Poles	Faceview	Housing Style	Part Number
5	<p>7/8"-16UN2</p>	<p>7/8-16UN2A</p>	MINDN-5MP-DP1
	<p>7/8"-16UN2</p>	<p>7/8-16UN2B FEMALE THREAD</p>	MINDN-5FP-DP1
MDC Terminating Plugs			
5	<p>M12 x 1</p>	<p>M12x1 MALE THREADS</p>	MDCDN-5MP-DP1
	<p>M12 x 1</p>	<p>M12x1 FEMALE THREADS</p>	MDCDN-5FP-DP1

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MINDN-5FP-DP1 becomes MINDN-5FP-DP1-SS)

Specifications:

Body: Oil Resistant Black PVC
 Contacts: Copper Alloy with Gold Plating
 Coupling Nut: Nickel Plated Brass
 Temperature: -40°C to +105°C (-40°F to +221°F)

K DeviceNet