



MDC (M12) Series Splitters

4 & 5 Conductor MDC Series Splitters



Splitters | 60 Volt, 4 amps | IP67 Rating

H

Micro-DC (M12) Series Cordsets

Housing Style	Rating	Part Number	Circuit
	60V 4A	MDC-44YFF	
	60V 4A	MDC-45YFF	
	60V 4A	MDC-55YFF	

Specifications:

- Body: Oil Resistant PUR
- Insulator: Polyamide
- Contacts: Copper Alloy with Gold Plating
- Coupling Nut: Nickel Plated Brass
- O-Ring: BUNA-A
- Temperature: -40°C to +105°C (-40°F to +221°F)