



# Profibus-PA Series "T" Connectors

## 4 Conductor Profibus-PA Series "T" Connectors, 14-22AWG




"T" Connectors | Male to Female | MIN & MDC | 300 Volt, 4/8 amps MAX | IP67 Rating



MIN Male to Two MIN Female "T" Connectors					
# of Poles	Male Faceview	Rating	Part Number	Wiring	Female Faceview
4	<p>7/8"-16UN2</p>	300V 8A	PBIN-4MFF-T-SS	1 to 1 to 1 2 to 2 to 2 3 to 3 to 3 4 to 4 to 4	<p>7/8"-16UN2</p>
MIN Male to MIN & MDC Female "T" Connectors					
4	<p>7/8"-16UN2</p>	300V 4A	PBINDC-4MFF-T-SS	1 to 1 to 1 2 to 2 to 2 3 to 3 to 3 4 to 4 to 4	<p>M12 x 1</p>

Profibus-PA Series

0



### Specifications:

- Body: Oil Resistant Yellow PVC
- Contacts: Copper Alloy with Gold Plating
- Coupling Nut: Stainless Steel
- Temperature: -40°C to +105°C (-40°F to +221°F)