



7/8" MIN Series Size I Accessories

MIN Series Size I Accessories



Closure Caps & Plugs | Adapter Coupling | IP67 Rating

A

MIN Series Size I Cordsets

Metal/Plastic Closure Caps				
Closure Style	Part Number	Material	Threads	Mounting Hole Size
	MIN-CAP	Nickel Plated Brass	Female	0.13"
	MIN-CAP-CBLY	Nickel Plated Brass	Female	1.3" (For Use on Cables)
	MIN-CAP-PASW	Polyamide NBR with Tether***	Female	0.76"
Metal Closure Plugs				
	MIN-PLUG	Nickel Plated Brass	Male	0.13"
	MIN-PLUG-CBLY	Nickel Plated Brass	Male	1.3" (For Use on Cables)
	MIN-PLUG-NC	Clear Anodized Aluminum	Male	N/A

NBR tether and stainless steel lanyard are available for all MIN-CAP and MIN-PLUG. Please consult the factory for part number and availability.

***Tether mounts under receptacles with 1/2" NPT, M20 or M25 mounting threads and also serves as a gasket.

Adapter Coupling	Part Number	Material	Threads
	MIN-XMP-AD	Nickel Plated Brass	Male
	MIN-XMP-AD-SS	Stainless Steel	