



# 1 3/8" MIN Power Series Adapter Plugs

3 & 4 Conductor PMIN (1.375"-16UN) to MINH (7/8"-16UN) Adapter Plugs



Adapter Plugs | PMIN (1 3/8") to MINH (7/8") | 600 Volt | IP67 Rating



Housing Style	Part Number	Rating	Male Faceview	Connection Diagram	Female Faceview
	PMINH-3MFP-AD1	600V 18A	<p>1.375"-16UN2</p>		<p>7/8"-16UN2</p>
	PMINH-4MFP-AD1	600V 15A	<p>1.375"-16UN2</p>		<p>7/8"-16UN2</p>

**D**  
PMIN Cordsets

**Specifications:**

- Body: Oil Resistant Yellow PVC
- Contacts: Copper Alloy with Gold Plating
- Coupling Nuts: Nickel Plated Brass
- Inserts: Oil Resistant PVC
- O-Ring: NBR