



MIL-SPEC Series Cordsets

5, 6 & 7 Conductor 5015 Industrial Equiv. Cordsets, 16/18AWG



Straight Male Cordsets | Size 14S | 600V, 8A | 300V, 8A | IP67 Rating



F
MIL-SPEC

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MS14S-5MP-** (Yellow)	PVC STOOW 5 X 16 AWG 600V, 8A -40°C to 105°C 13.1mm OD	Industry Standard PVC	North American A. White B. Red C. Green/Yellow D. Orange E. Black	 14S-5 0.8750"-20UNEF
	MS14S-5MP-**-B (Black)				
	MS14SM-5MP-**	Yellow PVC STOOW With Foil Shield 5 X 16 AWG 600V, 8A -40°C to 80°C 13.1mm OD	Industry Standard PVC Foil Shield		
	MS14SW-5MP-**	Yellow TPE SEOWW 5 X 16 AWG 600V, 8A -40°C to 80°C 13.1mm OD	Weld Slag Resistant TPE		
MS14SP-5MPX-**	Yellow PUR AWM 5 X 18 AWG 300V, 8A -40°C to 80°C 13.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR			
	MS14S-6MP-**	Yellow PVC STOOW 6 X 16 AWG 600V, 8A -40°C to 105°C 13.3mm OD	Industry Standard PVC	North American A. White B. Red C. Green/Yellow D. Orange E. Black F. Blue	 14S-6 0.8750"-20UNEF
	MS14S-6MPX-**	Yellow PVC SJTOOW 6 X 18 AWG 300V, 8A -40°C to 105°C 10.1mm OD	Industry Standard PVC		
	MS14SP-6MPX-**	Yellow PUR AWM 6 X 18 AWG 300V, 8A -40°C to 105°C 10.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MS14S-7MPX-**	Yellow PVC SJTOOW 7 X 18 AWG 300V, 8A -40°C to 105°C 10.1mm OD	Industry Standard PVC	North American A. White/Black B. Black C. White D. Red E. Orange F. Blue G. Green/Yellow	 14S-7 0.8750"-20UNEF
	MS14SP-7MPX-**	Yellow PUR AWM 7 X 18 AWG 300V, 8A -40°C to 105°C 10.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		

** Lengths in meters. Standard Cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated aluminum, for black anodized aluminum coupling nut add a "-BA" suffix. (e.g. MS14S-5MP-1M becomes MS14S-5MP-1M-BA)