



MIL-SPEC Series Cordsets

2 & 3 Conductor 5015 Industrial Equiv. Cordsets, 16AWG



Straight Female Cordsets | Size 10SL | 600 Volt, 13 amps | IP67 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MS10SL-2FP-**	Yellow PVC ST00W 2 X 16 AWG 600V, 13A -40°C to +150°C 9.5mm OD	Industry Standard PVC	North American A. White B. Black	 10SL-2 0.6250"-24NEF
	MS10SL-3FP-** (Yellow) MS10SL-3FP-**-B (Black)	PVC ST00W 3 X 16 AWG 600V, 13A -40°C to 105°C 10mm OD	Industry Standard PVC		
	MS10SLP-3FP-**	Yellow PUR AWM 3 X 16 AWG 600V, 13A -40°C to 80°C 10mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR	North American A. Green/Yellow B. Black C. White	 10SL-3 0.6250"-24NEF
	MS10SLW-3FP-** (YELLOW) MS10SLW-3FP-**-B (BLACK)	TPE SE00W 3 X 16 AWG 600V, 13A -40°C to 80°C 10mm OD	Weld Slag Resistant TPE		

F
MIL-SPEC

** Lengths in meters. Standard Cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated aluminum, for black anodized aluminum coupling nut add a "-BA" suffix. (e.g. MS10SL-3FP-1M becomes MS10SL-3FP-1M-BA)