



MIL-SPEC Series Cordsets

2, 3 & 4 Conductor 5015 Industrial Equiv. Cordsets, 16AWG



Straight Female Cordsets | Size 14S | 600 Volt, 13/10 amps | IP67 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MS14S-2FP-**	Yellow PVC STOOW 2 X 16 AWG 600V, 13A -40°C to +150°C 9.5mm OD	Industry Standard PVC	North American A. White B. Black	 14S-2 0.8750"-20UNEF
	MS14S-3AFP-** MS14S-3BFP-** MS14S-3CFP-** (Yellow) MS14S-3AFP-**-B MS14S-3BFP-**-B MS14S-3CFP-**-B (Black)	PVC STOOW 3 X 16 AWG 600V, 13A -40°C to 105°C 10mm OD	Industry Standard PVC	North American A. Green/Yellow B. Black C. White	 14S-3A 0.8750"-20UNEF
	MS14SP-3AFP-** MS14SP-3BFP-** MS14SP-3CFP-**	Yellow PUR AWM 3 X 16 AWG 600V, 13A -40°C to 80°C 10mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		 14S-3B 0.8750"-20UNEF
	MS14SW-3AFP-** MS14SW-3BFP-** MS14SW-3CFP-** (YELLOW) MS14SW-3AFP-**-B MS14SW-3BFP-**-B MS14SW-3CFP-**-B (BLACK)	TPE SEOOW 3 X 16 AWG 600V, 13A -40°C to 80°C 10mm OD	Weld Slag Resistant TPE	North American A. Green/Yellow B. Black C. White	 14S-3C 0.8750"-20UNEF
	MS14S-4FP-** (YELLOW) MS14S-4FP-**-B (BLACK)	PVC STOOW 4 X 16 AWG 600V, 10A -40°C to 105°C 10.8mm OD	Industry Standard PVC	North American A. Black B. White C. Red D. Green/Yellow	 14S-4 0.8750"-20UNEF
	MS14SM-4FP-**	Yellow PVC STOOW With Foil Shield 4 X 16 AWG 600V, 10A -40°C to 80°C 10.8mm OD	Industry Standard PVC Foil Shield		
	MS14SW-4FP-**	Yellow TPE SEOOW 4 X 16 AWG 600V, 10A -40°C to 80°C 10.8mm OD	Weld Slag Resistant TPE		

** Lengths in meters. Standard Cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated aluminum, for black anodized aluminum coupling nut add a "BA" suffix. (e.g. MS14S-3FP-1M becomes MS14S-3FP-1M-BA)

Insert locking, where available, is indicated by placing 'A, B or C' after the pin count in the part number. (e.g. MS14S-3FP-** becomes MS14S-3AFP-**)

F
MIL-SPEC