



# 7/8" MIN Series Size I Receptacles

2, 3, 4, 5 & 6 Conductor MIN Series Size I Receptacles



Male-Female Through Panel Mount Receptacles | IP67 Rating



A

MIN Series Size I Receptacles

# of Poles	Male Faceview	Rating	Part Number	Wiring	Female Faceview
2	 7/8"-16UN2	600V 13A	MIN-2MFRF-TM	1 to 1 2 to 2	 7/8"-16UN2
3	 7/8"-16UN2	600V 13A	MIN-3MFRF-TM	1 to 1 2 to 2 3 to 3	 7/8"-16UN2
4	 7/8"-16UN2	600V 10A	MIN-4MFRF-TM	1 to 1 2 to 2 3 to 3 4 to 4	 7/8"-16UN2
5	 7/8"-16UN2	600V 8A	MIN-5MFRF-TM	1 to 1 2 to 2 3 to 3 4 to 4 5 to 5	 7/8"-16UN2
6	 7/8"-16UN2	600V 8A	MIN-6MFRF-TM	1 to 1 2 to 2 3 to 3 4 to 4 5 to 5 6 to 6	 7/8"-16UN2

**Specifications:**

- Shell: Nickel Plated Brass
- Insulator: 105°C, Oil Resistant Yellow PVC
- Contacts: Copper Alloy with Gold Plating
- Jam Nut: Nickel Plated Brass
- Thrust Washer: Zinc Die-Cast
- Sealing Washer: NBR
- Temperature: -40°C to 105°C (-40°F to +221°F)

