



7/8" MIN Series Size I Cordsets

3 Conductor MIN Series Size I Cordsets, 18AWG



Straight Male Cordsets | 300 Volt, 8 amps | IP67 Rating

A

MIN Series Size I Cordsets



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-3MPX-* (YELLOW) MIN-3MPX-* (BLACK)	PVC SJTOOW 3 X 18 AWG 300V, 8A -40°C to +105°C 8.5mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MIN-3MPX-*A	Yellow PVC SJTOOW 3 X 18 AWG 300V, 8A -40°C to +105°C 8.5mm OD	Industry Standard PVC	North American Auto Color Code 1. Green/Yellow 2. Red/Black 3. Red/White	 7/8"-16UN2
	MINE-3MPX-** (YELLOW) MINE-3MPX-** (BLACK)	PVC AWM 3 X 18 AWG 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Threaded Coupling Nut	European 1. Green/Yellow 2. Brown 3. Blue	 7/8"-16UN2
	MINC-3MPX-**	Yellow PVC AWM 3 X 18 AWG 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Threaded Coupling Nut	European Cenelec 1. Black 2. Brown 3. Blue	

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MIN-3MPX-3 becomes MIN-4MPX-3-SS)

See Page A-33 for Armored Cordset options.

Male Thread Option

For male threaded coupling replace "MPX" with "MPMX".

Male threads are standard on European color code cordsets.

(e.g. MIN-3MPX-3A becomes MIN-3MPMX-3A)

