



1 1/8" MIN Series Size III Receptacles

9, 10, 12 & 19 Conductor MIN Series Size III Receptacles, 16/18/22AWG



Front Mount Receptacles | European PG Threads | IP67 Rating



C

MIN Series Size III Receptacles

# of Poles	Male Faceview	Color Code	Rating	Wire AWG	Mounting Threads	Male Receptacles	Female Receptacles
9	 1 1/8"-16UN2	North American 1. Orange 6. Red 2. Blue 7. Green/Yellow 3. Red/Black 8. White/Black 4. Green/Black 9. Black 5. White	300V 4A	16 AWG	PG 13.5	MIN-9MR-1-PG13.5	MIN-9FR-1-PG13.5
					PG 16	MIN-9MR-1-PG16	MIN-9FR-1-PG16
			300V 4A	18 AWG	PG 13.5	MIN-9MR-1-18-PG13.5	MIN-9FR-1-18-PG13.5
					PG 16	MIN-9MR-1-18-PG16	MIN-9FR-1-18-PG16
			300V 4A	22 AWG	PG 13.5	MIN-9MR-1-22-PG13.5	MIN-9FR-1-22-PG13.5
					PG 16	MIN-9MR-1-22-PG16	MIN-9FR-1-22-PG16
10	 1 1/8"-16UN2	North American 1. Orange 6. Orange/Black 2. Blue 7. Red 3. White/Black 8. Green/Yellow 4. Red/Black 9. Black 5. Green/Black 10. White	300V 4A	16 AWG	PG 13.5	MIN-10MR-1-PG13.5	MIN-10FR-1-PG13.5
					PG 16	MIN-10MR-1-PG16	MIN-10FR-1-PG16
			300V 4A	18 AWG	PG 13.5	MIN-10MR-1-18-PG13.5	MIN-10FR-1-18-PG13.5
					PG 16	MIN-10MR-1-18-PG16	MIN-10FR-1-18-PG16
			300V 4A	22 AWG	PG 13.5	MIN-10MR-1-22-PG13.5	MIN-10FR-1-22-PG13.5
					PG 16	MIN-10MR-1-22-PG16	MIN-10FR-1-22-PG16
12	 1 1/8"-16UN2	North American 1. Orange 7. Blue/Black 2. Blue 8. Black/White 3. White/Black 9. Green/Yellow 4. Red/Black 10. Red 5. Green/Black 11. White 6. Orange/Black 12. Black	300V 4A	16 AWG	PG 13.5	MIN-12MR-1-PG13.5	MIN-12FR-1-PG13.5
					PG 16	MIN-12MR-1-PG16	MIN-12FR-1-PG16
			300V 4A	18 AWG	PG 13.5	MIN-12MR-1-18-PG13.5	MIN-12FR-1-18-PG13.5
					PG 16	MIN-12MR-1-18-PG16	MIN-12FR-1-18-PG16
			300V 4A	22 AWG	PG 13.5	MIN-12MR-1-22-PG13.5	MIN-12FR-1-22-PG13.5
					PG 16	MIN-12MR-1-22-PG16	MIN-12FR-1-22-PG16
19	 1 1/8"-16UN2	1. Violet 11. Black 2. Red 12. Green/Yellow*** 3. Gray 13. Yellow/Brown 4. Red/Blue 14. Brown/Green 5. Blue*** 15. White 6. Green 16. Yellow 7. Brown*** 17. Pink 8. White/Green 18. Gray/Brown 9. White/Yellow 19. Gray/Pink 10. White/Gray	300V 8A	3 x 18 AWG	PG 13.5	MIN-19MR-1-PG13.5	MIN-19FR-1-PG13.5
					PG 16	MIN-19MR-1-PG16	MIN-19FR-1-PG16
			300V 3A	16 x 22 AWG	PG 13.5	MIN-19MR-1-PG13.5	MIN-19FR-1-PG13.5
					PG 16	MIN-19MR-1-PG16	MIN-19FR-1-PG16

*** For the 19 pole, Blue, Brown and Green/Yellow are 18 AWG wires.
 12" leads are standard. Longer lead lengths are available, please consult the factory for part numbers.
 Other wire gauges and color codes are available, please consult the factory.

Specifications:

Shell: Clear Anodized Aluminum
 Insulator: 105° C, Oil Resistant Yellow PVC
 Contacts: Copper Alloy with Gold Plating
 O-Ring: NBR
 Temperature: -40°C to +105°C (-40°F to +221°F)

