



1 1/8" MIN Series Size III Cordsets

19 Conductor MIN Series Size III Cordsets, 18/22AWG



Right Angle Male & Female Cordsets | 300 Volt, 4 & 2 amps | IP67 Rating



Male Cordsets					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MINP-19MP-**-R	Black PUR AWM With Foil Shield 3 X 18 AWG 300V, 4A 16 x 22 AWG 300V, 2A -40°C to +80°C 11mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR Foil Shield	North American 1. Violet 2. Red 3. Gray 4. Red/Blue 5. Blue*** 6. Green 7. Brown*** 8. White/Green 9. White/Yellow 10. White/Gray 11. Black 12. Green/Yellow*** 13. Yellow/Brown 14. Brown/Green 15. White 16. Yellow 17. Pink 18. Gray/Brown 19. Gray/Pink	 1 1/8"-16UN2
Female Cordsets					
	MINP-19FP-**-R	Black PUR AWM With Foil Shield 3 X 18 AWG 300V, 4A 16 x 22 AWG 300V, 2A -40°C to +80°C 11mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR Foil Shield	North American 1. Violet 2. Red 3. Gray 4. Red/Blue 5. Blue*** 6. Green 7. Brown*** 8. White/Green 9. White/Yellow 10. White/Gray 11. Black 12. Green/Yellow*** 13. Yellow/Brown 14. Brown/Green 15. White 16. Yellow 17. Pink 18. Gray/Brown 19. Gray/Pink	 1 1/8"-16UN2

C

MIN Series Size III Cordsets

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 . Consult factory for other lengths.

*** Blue, Brown and Green/Yellow are 18 AWG wires.

Standard coupling nut is anodized aluminum, for stainless steel coupling nut add a "-SS" suffix. (e.g. MINP-19MP-1M-R becomes MINP-19MP-1M-R-SS)

For male threaded coupling nut replace "MP" with "MPM". (e.g. MIN-19MP-1M-R becomes MIN-19MPM-1M-R)