



# 1 3/8" MIN Power Series Cordsets

3 Conductor MIN Power Series Cordsets, 10, 12 & 14AWG



Straight Male Cordsets | 600 Volt | IP67 Rating



D  
PMIN Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	PMIN-30MP-**	Gray PVC STOOW <b>3 X 10 AWG</b> 600V, 30A -40°C to +105°C 16.6mm OD	Industry Standard PVC	<b>North American</b> 1. Green/Yellow 2. Black 3. White	 1.375"-16UN2
	PMIN-34MP-**	Gray PVC STOOW <b>3 X 14 AWG</b> 600V, 18A -40°C to +105°C 13.6mm OD			
	PMINW-30MP-**-C011	Black TPE TC-ER <b>3 X 10AWG</b> 600V, 30A -40°C to +90°C 11.9mm OD	TC-ER, FT4 Weld Slag Resistant TPE	<b>North American</b> 1. Green/Yellow 2. Black 3. White	 1.375"-16UN2
	PMINW-32MP-**-C011	Black TPE TC-ER <b>3 X 12AWG</b> 600V, 25A -40°C to +90°C 10.2mm OD			
	PMINW-34MP-**-C011	Black TPE TC-ER <b>3 X 14AWG</b> 600V, 18A -40°C to +90°C 8.89mm OD			

\*\* Lengths in meters. Standard cable lengths are 1, 2, 5, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling add -SS suffix. (e.g. PMIN-30MP-1M becomes PMIN-30MP-1M-SS)