



1 3/8" MIN Power Series Cordsets

3 Conductor MIN Power Series Cordsets, 10, 12 & 14AWG



Double Ended Cordsets | 600 Volt | IP67 Rating



D
PMIN Cordsets

Male Faceview	Cables	Straight Male to Straight Female	Right Angle Male to Right Angle Female	Right Angle Male to Straight Female	Straight Male to Right Angle Female
<p>1.375"-16UN2</p>	Gray PVC STOOW 3 X 10 AWG 600V, 30A -40°C to +105°C 16.6mm OD	PMIN-30MFP-**	PMIN-30MFP-**-R	PMIN-30MRFP-**	PMIN-30MFRP-**
	Gray PVC STOOW 3 X 14 AWG 600V, 18A -40°C to +105°C 13.6mm OD	PMIN-34MFP-**	PMIN-34MFP-**-R	PMIN-34MRFP-**	PMIN-34MFRP-**
<p>1.375"-16UN2</p>	Black TPE TC-ER 3 X 10AWG 600V, 30A -40°C to +90°C 11.9mm OD	PMINW-30MFP-**-C011	PMINW-30MFP-**-R-C011	PMINW-30MRFP-**-C011	PMINW-30MFRP-**-C011
	Black TPE TC-ER 3 X 12AWG 600V, 25A -40°C to +90°C 10.2mm OD	PMINW-32MFP-**-C011	PMINW-32MFP-**-R-C011	PMINW-32MRFP-**-C011	PMINW-32MFRP-**-C011
	Black TPE TC-ER 3 X 14AWG 600V, 18A -40°C to +90°C 8.89mm OD	PMINW-34MFP-**-C011	PMINW-34MFP-**-R-C011	PMINW-34MRFP-**-C011	PMINW-34MFRP-**-C011

** Lengths in meters. Standard cable lengths are 1, 2, 5, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling add -SS suffix. (e.g. PMIN-30MFP-1M becomes PMIN-30MFP-1M-SS)

Straight

Right Angle



Male Plug

Female Plug

Male Plug

Female Plug