



7/8" MIN Power Series Cordsets

3 & 4 Conductor MIN Power Series Size I Cordsets, 14AWG



Straight & Right Angle Cordsets | 600 Volt, 18 amps | 600 Volt, 15 amps | IP67 Rating



D

MIN Power Cordsets

Male Straight					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MINH-3MP-**	Gray PVC STOOW 3 X 14 AWG 600V, 18A -40°C to +105°C 13.7mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINH-4MP-**	Gray PVC STOOW 4 X 14 AWG 600V, 15A -40°C to +105°C 14.9mm OD	Industry Standard PVC	North American 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
Female Straight					
	MINH-3FP-**	Gray PVC STOOW 3 X 14 AWG 600V, 18A -40°C to +105°C 13.7mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINH-4FP-**	Gray PVC STOOW 4 X 14 AWG 600V, 15A -40°C to +105°C 14.9mm OD	Industry Standard PVC	North American 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
Female Right Angle					
	MINH-3FP-**-R	Gray PVC STOOW 3 X 14 AWG 600V, 18A -40°C to +105°C 13.7mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINH-4FP-**-R	Gray PVC STOOW 4 X 14 AWG 600V, 15A -40°C to +105°C 14.9mm OD	Industry Standard PVC	North American 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2

** Lengths in meters. Standard cable lengths are 1, 2, 5, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless coupling nut add a "SS" suffix. (e.g. MINH-4FP-3 becomes MINH-4FP-3-SS)