



MCV (M23) Series Cordsets

12 Conductor M23 Series Cordsets, 18/22AWG



Straight Female Cordsets | 300 Volt, 6 amps | 300 Volt, 6 & 2 amps | IP67 Rating



18 AWG					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MCVW-12FPX-**-N01	Black TPE AWM 12 X 18 AWG 300V, 6A -40°C to +105°C 9.9mm OD	Weld Slag Resistant TPE	Black Numbered Wires #1-11 Green/Yellow #12	 M23 x 1
18 & 22 AWG					
	MCVP-12FP-**-	Black PUR AWM With Foil Shield 3 X 18 AWG 300V, 6A 9 X 22 AWG 300V, 2A -40°C to +80°C 8.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR Foil Shield	1. Brown*** 2. Brown/White 3. Blue*** 4. White 5. Green 6. Yellow 7. Gray 8. Pink 9. Red 10. Black 11. Violet 12. Green/Yellow***	 M23 x 1
	MCVW-12FP-**-	Black TPE AWM With Foil Shield 3 X 18 AWG 300V, 6A 9 X 22 AWG 300V, 2A -40°C to +80°C 8.1mm OD	Weld Slag Resistant TPE Foil Shield		

E
M23 Series

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

*** Brown, Blue and Green/Yellow are 18AWG

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MCVP-12FP-1M becomes MCV-12FP-1M-SS)