



MCV (M23) Series Cordsets

16 & 17 Conductor M23 Series Cordsets, 18AWG



Straight Female Cordsets | 150 Volt, 5 amps | IP67 Rating



16 Pole					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MCV-16FPX-**-N01	Black PVC AWM 16 X 18 AWG 150V, 5A -40°C to +90°C 13.6mm OD	PVC ITC-ER/PLTC-ER	Black Numbered Wires #1-15 Green/Yellow #16	<p>M23 x 1</p>
	MCV-16FPX-**-C010	Black PVC AWM 16 X 18 AWG 150V, 5A -40°C to +90°C 12.1mm OD	PVC ITC-ER/PLTC-ER	1. White 9. Black 2. Brown 10. Violet 3. Green 11. Gray/Pink 4. Yellow 12. Red/Blue 5. Gray 13. White/Green 6. Pink 14. Brown/Green 7. Blue 15. White/Yellow 8. Red 16. Yellow/Brown	
17 Pole					
	MCV-17FPX-**-N01	Black PVC AWM 17 X 18 AWG 150V, 5A -40°C to +90°C 13.6mm OD	PVC ITC-ER/PLTC-ER	Black Numbered Wires #1-16 Green/Yellow #17	<p>M23 x 1</p>
	MCV-17FPX-**-C010	Black PVC AWM 17 X 18 AWG 150V, 5A -40°C to +90°C 12.1mm OD	PVC ITC-ER/PLTC-ER	1. White 10. Violet 2. Brown 11. Gray/Pink 3. Green 12. Red/Blue 4. Yellow 13. White/Green 5. Gray 14. Brown/Green 6. Pink 15. White/Yellow 7. Blue 16. Yellow/Brown 8. Red 17. White/Gray 9. Black	

E
M23 Series

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MCV-16FPX-1M-N01 becomes MCV-16FPX-1M-N01-SS)