





MIL-SPEC Series Receptacles

2 & 3 Conductor 5015 Industrial Equiv. Receptacles



Panel Mount Receptacles | Size 10SL | IP67 Rating

F
MIL-SPEC

# of Poles	Male Faceview	Color Code	Rating	Wire AWG	Male Receptacles	Female Receptacles
2	 <p>10SL-2 0.6250"-24NEF</p>	North American A. White B. Black	600V 13A	16 AWG	MS10SL-2MR-PM	MS10SL-2FR-PM
			300V 10A	18 AWG	MS10SL-2MR-18-PM	MS10SL-2FR-18-PM
			300V 4A	22 AWG	MS10SL-2MR-22-PM	MS10SL-2FR-22-PM
3	 <p>10SL-3 0.6250"-24NEF</p>	North American A. Green/Yellow B. Black C. White	600V 13A	16 AWG	MS10SL-3MR-PM	MS10SL-3FR-PM
			300V 10A	18 AWG	MS10SL-3MR-18-PM	MS10SL-3FR-18-PM
			300V 4A	22 AWG	MS10SL-3MR-22-PM	MS10SL-3FR-22-PM

12" leads are standard. Longer lead lengths are available, please consult the factory for part numbers.

Specifications:

Shell: Nickel Plated Zinc Diecast
 Insulator: PBT
 Contacts: Copper Alloy with Silver Plating
 Gasket: NBR
 Insert: PBT
 Temperature: -40°C to +105°C (-40°F to +221°F)

