



MIL-SPEC Series Receptacles

4, 5, 6 & 7 Conductor 5015 Industrial Equiv. Receptacles



Panel Mount Receptacles | Size 14S | IP67 Rating

F
MIL-SPEC

# of Poles	Male Faceview	Color Code	Rating	Wire AWG	Male Receptacles	Female Receptacles
4	 14S-4 0.8750"-20UNEF	North American A. Black B. White C. Red D. Green/Yellow	600V 10A	16 AWG	MS14S-4MR-PM	MS14S-4FR-PM
			300V 5.5A	18 AWG	MS14S-4MR-18-PM	MS14S-4FR-18-PM
			300V 4A	22 AWG	MS14S-4MR-22-PM	MS14S-4FR-22-PM
5	 14S-5 0.8750"-20UNEF	North American A. White B. Red C. Green/Yellow D. Orange E. Black	600V 8A	16 AWG	MS14S-5MR-PM	MS14S-5FR-PM
			300V 8A	18 AWG	MS14S-5MR-18-PM	MS14S-5FR-18-PM
			300V 4A	22 AWG	MS14S-5MR-22-PM	MS14S-5FR-22-PM
6	 14S-6 0.8750"-20UNEF	North American A. White B. Red C. Green/Yellow D. Orange E. Black F. Blue	600V 8A	16 AWG	MS14S-6MR-PM	MS14S-6FR-PM
			300V 8A	18 AWG	MS14S-6MR-18-PM	MS14S-6FR-18-PM
			300V 4A	22 AWG	MS14S-6MR-22-PM	MS14S-6FR-22-PM
7	 14S-7 0.8750"-20UNEF	North American A. White/Black B. Black C. White D. Red E. Orange F. Blue G. Green/Yellow	600V 5A	16 AWG	MS14S-7MR-PM	MS14S-7FR-PM
			300V 8A	18 AWG	MS14S-7MR-18-PM	MS14S-7FR-18-PM
			300V 3A	22 AWG	MS14S-7MR-22-PM	MS14S-7FR-22-PM

12" leads are standard. Longer lead lengths are available, please consult the factory for part numbers.

Specifications:

Shell: Nickel Plated Zinc Diecast
 Insulator: PBT
 Contacts: Copper Alloy with Silver Plating
 Gasket: NBR
 Insert: PBT
 Temperature: -40°C to +105°C (-40°F to +221°F)

