



MAC (1/2"-20) Series Cordsets

2 & 3 Conductor MAC Series Cordsets, 18/20/22AWG



Straight Male Cordsets | 300 Volt, 4 amps | IP67 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MAC-2MP-**	Yellow PVC AWM 2 X 20 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC	1. Brown 2. Blue	 1/2"-20
	MAC-3MPX-** (Yellow) MAC-3MPX-**-B (Black)	PVC AWM 3 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	1. Green/Yellow 2. Red/Black 3. Red/White	 1/2"-20
MAC-3MP-**	Yellow PVC AWM 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC			
MACB-3MP-**	Yellow PVC AWM With Braided Shield 3 X 22 AWG 300V, 4A -40°C to +105°C 5.8mm OD	Industry Standard PVC Braided Shield			
MACP-3MP-**	Yellow PUR AWM 3 X 22 AWG 300V, 4A -40°C to +80°C 5.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR			

G

Micro-AC Series (1/2"-20) Cordsets

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is Nickel Plated Brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MAC-3MPX-1M becomes MAC-3MPX-1M-SS)