



MDC (M12) Series Cordsets

2 & 3 Conductor MDC Series Cordsets, 18/20/22AWG



Right Angle Male Cordsets | 300 Volt, 4 amps | IP67 Rating



H

Micro-DC (M12) Series Cordsets

| Connector Body Style | Part Number | Cables | Features | Color Code | Faceview |
|----------------------|---------------|---|--|---------------------------------|----------|
| | MDC-2MPX-**-R | Yellow PVC AWM 2 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD | Industry Standard PVC | 3. Brown 4. Blue | |
| | MDC-2MP-**-R | Yellow PVC AWM 2 X 20 AWG 300V, 4A -40°C to +105°C 5mm OD | Industry Standard PVC | | |
| | MDC-3MPX-**-R | Yellow PVC AWM 3 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD | Industry Standard PVC | 1. Brown 3. Blue 4. Black | |
| | MDC-3MP-**-R | Yellow PVC AWM 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD | Industry Standard PVC | | |
| | MDCM-3MP-**-R | Yellow PVC AWM With Foil Shield 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD | Industry Standard PVC Foil Shield | | |
| | MDCP-3MP-**-R | Yellow PUR AWM 3 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD | Oil and Cutting Fluid Resistant Cut Resistant PUR | | |

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix.(e.g. MDC-3MPX-1M-R becomes MDC-3MPX-1M-R-SS)