



MDC (M12) Series Cordsets

5 & 6 Conductor MDC Series Cordsets, 22/24AWG



Right Angle Male Cordsets | 300V, 4A | 60V, 2A | IP67 Rating



H

Micro-DC (M12) Series Cordsets

| Connector Body Style | Part Number | Cables | Features | Color Code | Faceview |
|----------------------|---|---|--|---|-------------|
| | MDC-5MPX-**-R | Yellow PVC AWM 5 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD | Industry Standard PVC | 1. Brown 2. White 3. Blue 4. Black 5. Gray | M12 x 1 |
| | MDC-5MP-**-R (Yellow) MDC-5MP-**-R-B (Black) | PVC AWM 5 X 22 AWG 300V, 4A -40°C to +105°C 5.8mm OD | Industry Standard PVC | | |
| | MDCM-5MP-**-R | Yellow PVC AWM With Foil Shield 5 X 22 AWG 300V, 4A -40°C to +105°C 5.8mm OD | Industry Standard PVC Foil Shield | | |
| | MDCP-5MP-**-R | Yellow PUR AWM 5 X 22 AWG 300V, 4A -40°C to +80°C 5.8mm OD | Oil and Cutting Fluid Resistant Cut Resistant PUR | | |
| | MDCWF-5MP-**-R-B | Black TPE AWM 5 X 22 AWG 300V, 4A -40°C to +80°C 5.2mm OD | Hi-Flex Weld Slag Resistant TPE | | |
| | MDCM-6MP-**-R | Yellow PVC AWM With Foil Shield 6 X 24 AWG 60V, 2A -40°C to +105°C 5.8mm OD | Industry Standard PVC Foil Shield | 1. Brown 2. White 3. Blue 4. Black 5. Gray 6. Pink | M12 x 1 |

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Black and gray cables are available on some versions, please consult the factory.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDC-5MP-1M-R becomes MDC-5MP-1M-R-SS)