



MDC (M12) Series Cordsets

6 Conductor MDC Series Cordsets, 24AWG



Double Ended Cordsets | Straight | 60 Volt, 2 amps | IP67 Rating



Shielded to coupling nut versions are not UL listed.




Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
<p>M12 x 1</p>	MDCM-6MFP-**	Yellow PVC AWM With Foil Shield 6 X 24 AWG 60V, 2A -40°C to +105°C 5.8mm OD	Industry Standard PVC Foil Shield	1. Brown 2. White 3. Blue 4. Black 5. Gray 6. Pink	<p>M12 x 1</p>
	MDCM-6MFPS-**	Yellow PVC AWM With Foil Shield 6 X 24 AWG 60V, 2A -40°C to +80°C 5.8mm OD	Industry Standard PVC Foil Shield to the Coupling Nut		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Black and gray cables are available on some versions, please consult the factory.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MDCM-6MFP-1M becomes MDCM-6MFP-1M-SS)



Male - Female Extension

H

Micro-DC (M12) Series Cordsets