



# MDC (M12) Series Cordsets

12 Conductor MDC Series Cordsets, 24AWG



Double Ended Cordsets | Straight | 60 Volt, 2 amps | IP67 Rating




Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
<p>M12 x 1</p>	MDCM-12MFP-**-B	Black PVC AWM With Foil Shield <b>12 X 24 AWG</b> 60V, 2A -40°C to +105°C 6.7mm OD	Industry Standard PVC Foil Shield	1. White 2. Brown 3. Green 4. Yellow 5. Gray 6. Pink 7. Blue 8. Red 9. Orange 10. Tan 11. Black 12. Violet	<p>M12 x 1</p>
	MDCPM-12MFP-**-B	Black PUR AWM With Foil Shield <b>12 X 24 AWG</b> 60V, 2A -40°C to +80°C 6.7mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR Foil Shield		

\*\* Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Gray cables are available on some versions, please consult the factory.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDCM-12MFP-1M-B becomes MDCM-12MFP-1M-B-SS)



Male - Female Extension

H

Micro-DC (M12) Series Cordsets