



MDC (M12) Series Cordsets

2 & 3 Conductor MDC Series Cordsets, 18/20/22AWG



Straight Male Cordsets | 300 Volt, 4 amps | IP67 Rating



H

Micro-DC (M12) Series Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MDC-2MPX-**	Yellow PVC AWM 2 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	3. Brown 4. Blue	 M12x1
	MDC-2MP-**	Yellow PVC AWM 2 X 20 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC		
	MDC-3MPX-**	Yellow PVC AWM 3 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	1. Brown 3. Blue 4. Black	 M12x1
	MDC-3MP-** (Yellow) MDC-3MP-**-B (Black)	PVC AWM 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC		
	MDCM-3MP-**	Yellow PVC AWM With Foil Shield 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield		
	MDCP-3MP-**	Yellow PUR 3 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDC-3MPX-1M becomes MDC-3MPX-1M-SS)