

# Euro-AC (M12) Series Cordsets

3, 4 & 5 Conductor MEC Series Cordsets, 22AWG



Straight Male Cordsets | 300 Volt, 4 amps | IP67 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MEC-3MP-**	Gray PVC AWM <b>3 X 22 AWG</b> 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC	<ol style="list-style-type: none"> <li>1. Brown</li> <li>2. Blue</li> <li>3. Not Used</li> <li>4. Green/Yellow</li> <li>5. Not Used</li> </ol>	<p>M12 x 1</p>
	MEC-4MP-**	Gray PVC AWM <b>4 X 22 AWG</b> 300V, 4A -40°C to +105°C 5.8mm OD	Industry Standard PVC	<ol style="list-style-type: none"> <li>1. Brown</li> <li>2. Blue</li> <li>3. Black</li> <li>4. Green/Yellow</li> <li>5. Not Used</li> </ol>	<p>M12 x 1</p>
	MEC-5MP-**	Gray PVC AWM <b>5 X 22 AWG</b> 300V, 4A -40°C to +105°C 5.8mm OD	Industry Standard PVC	<ol style="list-style-type: none"> <li>1. Brown</li> <li>2. White</li> <li>3. Blue</li> <li>4. Black</li> <li>5. Green/Yellow</li> </ol>	<p>M12 x 1</p>

\*\* Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a “-SS” suffix. (e.g. MEC-4MP-1M becomes MEC-4MP-1M-SS)