

NAN (M8) Series Snap-On Cordsets

3 & 4 Conductor NAN Series Cordsets, 24AWG



Straight/Right Angle Male Cordsets | Snap-On Style | 60 Volt, 3 amps | IP67 Rating



Snap-On Style: Male Straight Plugs					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	NAN-3MP-**	Black PVC AWM 3 X 24 AWG 60V, 3A -40°C to +105°C 4.5mm OD	Industry Standard PVC	1. Brown 2. Not Used 3. Blue 4. Black	
	NANP-3MP-**	Black PUR AWM 3 X 24 AWG 60V, 3A -40°C to +80°C 4.5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	NAN-4MP-**	Black PVC AWM 4 X 24 AWG 60V, 3A -40°C to +105°C 4.5mm OD	Industry Standard PVC	1. Brown 2. White 3. Blue 4. Black	
	NANP-4MP-**	Black PUR AWM 4 X 24 AWG 60V, 3A -40°C to +80°C 4.5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.