



DeviceNet Series MIN/MDC Cordsets

5 Conductor DeviceNet Series Cordsets, 15/18AWG & 22/24AWG



Straight Female Cordsets | 600 Volt, 8 amps | 300 Volt, 4 amps | IP67 Rating



MIN Trunk Cordsets - Thick Cable					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MINDT-5FP-**	Gray PVC Trunk Cable AWM With Braided Shield 2 X 15 AWG 2 X 18 AWG 1 x 18 AWG (Drain) 600V, 8A -40°C to +80°C 11.2mm OD	Industry Standard PVC Braided Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	 7/8"-16UN2
MIN & MDC Drop Cordsets - Thin Cable					
	MINDD-5FP-**	Gray PVC Drop Cable AWM With Braided Shield 2 X 22 AWG 2 X 24 AWG 1 x 22 AWG (Drain) 300V, 4A -40°C to +80°C 7.4mm OD	Industry Standard PVC Braided Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	 7/8"-16UN2
	MDCDD-5FP-**	Gray PVC Drop Cable AWM With Braided Shield 2 X 22 AWG 2 X 24 AWG 1 x 22 AWG (Drain) 300V, 4A -40°C to +80°C 7.4mm OD	Industry Standard PVC Braided Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	 M12 x 1
	MDCUT-5FP-**	Gray PVC Drop Cable AWM With Foil Shield 2 X 24 AWG 2 X 24 AWG 1 x 24 AWG (Drain) 300V, 3A -40°C to +80°C 5.7mm OD	Industry Standard PVC Foil Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	 M12 x 1

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MINDD-5FP-1M becomes MINDD-5FP-1M-SS)

K
DeviceNet