



DeviceNet Series MIN Cordsets


5 Conductor DeviceNet Series Cordsets, 15/18AWG



Double Ended Cordsets | 600 Volt, 8 amps | 300 Volt, 4 amps | IP67 Rating



MIN Trunk Extension - Thick Cable					
Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
<p>7/8"-16UN2</p>	MINDT-5MFP-**-	Gray PVC Trunk Cable AWM With Braided Shield 2 X 15 AWG 2 X 18 AWG 1 x 18 AWG (Drain) 600V, 8A -40°C to +80°C 11.2mm OD	Industry Standard PVC MIN to MIN Braided Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	<p>7/8"-16UN2</p>
MIN Drop Extension - Thin Cable					
<p>7/8"-16UN2</p>	MINDD-5MFP-**-	Gray PVC Drop Cable AWM With Braided Shield 2 X 22 AWG 2 X 24 AWG 1 x 22 AWG (Drain) 300V, 4A -40°C to +80°C 7.4mm OD	Industry Standard PVC MIN to MIN Braided Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	<p>7/8"-16UN2</p>



Male(Male Thread) MIN to Female MIN Extension

MIN Male to MDC Female Extension - Thin Cable					
Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
<p>7/8"-16UN2</p>	MINDCDD-5MFP-**-	Gray PVC Drop Cable AWM With Braided Shield 2 X 22 AWG 2 X 24 AWG 1 x 22 AWG (Drain) 300V, 4A -40°C to +80°C 7.4mm OD	Industry Standard PVC MIN to MDC Braided Shield	1. Bare (Drain) 2. Red (V+) 3. Black (V-) 4. White (CAN_H) 5. Blue (CAN_L)	<p>M12 x 1</p>

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MINDCDD-5MFP-1M becomes MINDCDD-5MFP-1M-SS)



Male MIN to Female MDC Extension