




# Ethernet (M12) Series Etherplug Cordsets

8 Conductor Ethernet Series Cordsets, 24/26AWG



Double Ended Cordsets | 42 VDC, 1.5 amps | CAT5e | A-Coded | Twisted Pairs | IP67 Rating




Male Faceview	Cables	Features	Shield Type	Male to RJ45	Female to RJ45	
 M12 x 1	Teal PUR With Foil & Braided Shield <b>8 X 26 AWG</b> 60V, 2A -40°C to +75°C 6.3mm OD	Continuous-Flex Oil and Cutting Fluid Resistant Cut Resistant PUR Foil & Braided Shield	Shield to Coupling Nut	MDE45PB-8MSP-RJ45-**	MDE45PB-8FSP-RJ45-**	
			Shield to RJ45	MDE45PB-8MP-RJ45S-**	MDE45PB-8FP-RJ45S-**	
			Shield to Coupling Nut & RJ45	MDE45PB-8MSP-RJ45S-**	MDE45PB-8FSP-RJ45S-**	
		Teal TPE AWM With Foil & Braided Shield <b>8 X 24 AWG</b> 60V, 2A -40°C to +80°C 7.6mm OD	Continuous-Flex Weld Slag Resistant TPE Foil & Braided Shield	Shield to Coupling Nut	MDE45WB-8MSP-RJ45-**	MDE45WB-8FSP-RJ45-**
				Shield to RJ45	MDE45WB-8MP-RJ45S-**	MDE45WB-8FP-RJ45S-**
				Shield to Coupling Nut & RJ45	MDE45WB-8MSP-RJ45S-**	MDE45WB-8FSP-RJ45S-**

\*\* Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.


Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDE45-8FP-RJ45-1M becomes MDE45-8FP-RJ45-1M-SS)

### Mencom Standard Cable Color Code

M12	Color	RJ45
6	White/Orange	1
4	Orange	2
1	White/Blue	5
7	Blue	4
5	White/Green	3
8	Green	6
2	White/Brown	7
3	Brown	8



Male - RJ45 Extension



Female - RJ45 Extension