



Ethernet (M12) Series Etherplug Cordsets

4 Conductor Ethernet Series Cordsets, 24AWG



Right Angle Male Cordsets | 300 Volt, 3 amps | CAT5e | D-Coded | Twisted Pairs | IP67 Rating



Ethernet Series

L

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MDE45-4MP-**-R	Teal PVC AWM 4 X 24 AWG 300V, 3A -20°C to +80°C 6.1mm OD	Industry Standard PVC	1. White/Orange 2. White/Green 3. Orange 4. Green	 M12 x 1
	MDE45M-4MP-**-R	Teal PVC AWM With Foil Shield 4 X 26 AWG 300V, 3A -20°C to +80°C 6.6mm OD	Industry Standard PVC Foil Shield		
	MDE45P-4MP-**-R	Teal PUR AWM 4 X 24 AWG 300V, 3A -40°C to +80°C 5.6mm OD	Continuous-Flex Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MDE45PB-4MP-**-R	Teal PUR AWM With Foil & Braided Shield 4 X 24 AWG 300V, 3A -40°C to +80°C 6.4mm OD	Continuous-Flex Oil and Cutting Fluid Resistant Cut Resistant PUR Foil & Braided Shield		
	MDE45WB-4MP-**-R (Teal) MDE45WB-4MP-**-R-RD (Red)	TPE AWM With Foil & Braided Shield 4 X 24 AWG 300V, 3A -40°C to +80°C 6.6mm OD	Continuous-Flex Weld Slag Resistant TPE Foil & Braided Shield		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MDE45-4MP-1M-R becomes MDE45-4MP-1M-R-SS)