



Profibus-DP Series Cordsets

3 Conductor Profibus-DP Series Cordsets, 22AWG



Straight, Right Angle & Double Ended Cordsets | 300 Volt, 4 amps | IP67 Rating



Profibus-DP Series

N


Profibus-DP Male Cordsets					
Connector Body Style	Part Number	Cables	Features	Color Code	Male Faceview
	PBEC-3MP-**	Purple PVC PLTC/AWM With Foil Shield 2 X 22 AWG 300V, 4A -40°C to +80°C 8.6mm OD	Industry Standard PVC Foil Shield	1. N/C 2. Green (TxD) 3. N/C 4. Red (RxD) 5. Shield	<p>M12 x 1</p>

Profibus-DP Female Cordsets					
Connector Body Style	Part Number	Cables	Features	Color Code	Female Faceview
	PBEC-3FP-**	Purple PVC PLTC/AWM With Foil Shield 2 X 22 AWG 300V, 4A -40°C to +80°C 8.6mm OD	Industry Standard PVC Foil Shield	1. N/C 2. Green (TxD) 3. N/C 4. Red (RxD) 5. Shield	<p>M12 x 1</p>
	PBEC-3FP-**-R	Purple PVC PLTC/AWM With Foil Shield 2 X 22 AWG 300V, 4A -40°C to +80°C 8.6mm OD	Industry Standard PVC Foil Shield	1. N/C 2. Green (TxD) 3. N/C 4. Red (RxD) 5. Shield	<p>M12 x 1</p>

Male - Female Extension Cables					
Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
<p>M12 x 1</p>	PBEC-3MFP-**	Purple PVC PLTC/AWM With Foil Shield 2 X 22 AWG 300V, 4A -40°C to +80°C 8.6mm OD	Industry Standard PVC Foil Shield	1. N/C 2. Green (TxD) 3. N/C 4. Red (RxD) 5. Shield	<p>M12 x 1</p>

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. PBEC-3FP-1M becomes PBEC-3FP-1M-SS)



Male - Female Extension