



# 7/8" MIN Series Size I Cordsets

5 Conductor MIN Series Size I Cordsets, 18AWG



Straight Male Cordsets | 300 Volt, 5.5 amps | IP67 Rating

A

MIN Series Size I Cordsets



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
<p>7/8"-16UN2B</p>	MIN-5MPX-* (YELLOW)  MIN-5MPX-* (BLACK)	PVC AWM <b>5 X 18 AWG</b> 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	<b>North American</b> 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	 7/8"-16UN2
	MINP-5MPX-*	Yellow PUR AWM <b>5 X 18 AWG</b> 300V, 5.5A -40°C to +80°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
<p>7/8"-16UN2B</p>	MIN-5MPX-*A (YELLOW)  MIN-5MPX-*A-B (BLACK)	PVC AWM <b>5 X 18 AWG</b> 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	<b>North American Auto Color Code</b> 1. Red/White 2. Red 3. Green/Yellow 4. Red/Yellow 5. Red/Black	 7/8"-16UN2
	MINE-5MPX-**	Yellow PVC AWM <b>5 X 18 AWG</b> 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Threaded Coupling Nut	<b>European</b> 1. Black 2. Blue 3. Green/Yellow 4. Brown 5. White	 7/8"-16UN2

\* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

\*\* Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-5MPX-3 becomes MIN-5MPX-3-SS)

See Page A-33 for Armored Cordset options.

## Male Thread Option

For male threaded coupling replace "MPX" with "MPMX".

Male threads are standard on European color code cordsets.

(e.g. MIN-5MPX-3 becomes MIN-5MPMX-3)

