



7/8" MIN Series Size I Cordsets

6 & 14 Conductor MIN Series Size I Cordsets, 18/22AWG



Straight Female Cordsets | 300 Volt, 5.5 amps | 300 Volt, 6 & 1 amps | IP67 Rating



A

MIN Series Size I Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-6FPX-*	Yellow PVC SJTOOW 6 X 18 AWG 300V, 5.5A -40°C to +105°C 10.1mm OD	Industry Standard PVC	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black 6. Blue	 7/8"-16UN2
	MINP-6FPX-*	Yellow PUR AWM 6 X 18 AWG 300V, 5.5A -40°C to +80°C 8.5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MINE-6FPX-**	Yellow PVC SJTOOW 6 X 18 AWG 300V, 5.5A -40°C to +105°C 10.1mm OD	Industry Standard PVC	European 1. Green 2. White 3. Blue 4. Gray 5. Yellow 6. Brown	 7/8"-16UN2
	MINP-14FP-**	Black PUR AWM 2 X 18 AWG 300V, 6A 12 x 22 AWG 300V, 1A -40°C to +80°C 8.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR	North American 1. Gray/Pink 2. White/Green 3. White/Yellow 4. Brown*** 5. Brown/Yellow 6. Blue*** 7. Yellow 8. Green 9. Pink 10. White 11. Red/Blue 12. Brown/Green 13. Gray 14. Red	 7/8"-16UN2

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

*** Brown and Blue are 18AWG wires.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-6FPX-3 becomes MIN-6FPX-3-SS)

See Page A-33 for Armored Cordset options.