



7/8" MIN Series Size I Cordsets

3 & 4 Conductor MIN Series Size I Cordsets, 18AWG











Right Angle Female Cordsets | 300 Volt, 8 amps | 300 Volt, 5,5 amps | IP67 Rating



A

MIN Series Size I Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-3FPX-*R (YELLOW) MIN-3FPX-*R-B (BLACK)	PVC SJTOOW 3 X 18 AWG 300V, 8A -40°C to +105°C 8.5mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MIN-3FPX-*A-R	Yellow PVC SJTOOW 3 X 18 AWG 300V, 8A -40°C to +105°C 8.5mm OD	Industry Standard PVC	North American Auto Color Code 1. Green/Yellow 2. Red/Black 3. Red/White	
	MINE-3FPX-**R (YELLOW) MINE-3FPX-**R-B (BLACK)	PVC AWM 3 X 18 AWG 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Threaded Coupling Nut	European 1. Green/Yellow 2. Brown 3. Blue	 7/8"-16UN2
	MINC-3FPX-**R	Yellow PVC AWM 3 X 18 AWG 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Threaded Coupling Nut	European Cenelec 1. Black 2. Brown 3. Blue	
	MIN-4FPX-*R	Yellow PVC AWM 4 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	North American 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
	MINC-4FPX-**R	PVC AWM 4 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	European Cenelec 1. Brown 2. White 3. Blue 4. Black	 7/8"-16UN2
	MINCP-4FPX-**R	Yellow PUR AWM 4 X 18 AWG 300V, 5.5A -40°C to +80°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MINCW-4FPX-**R	Yellow TPE AWM 4 X 18 AWG 300V, 5.5A -40°C to +80°C 7.4mm OD	Weld Slag Resistant TPE		

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-4FPX-3-R-SS becomes MIN-4FPX-3-R-SS)

See Page A-33 for Armored Cordset options.