



7/8" MIN Series Size I Cordsets

5 & 6 Conductor MIN Series Size I Cordsets, 18AWG



Right Angle Female Cordsets | 300 Volt, 5.5 amps | IP67 Rating



A
MIN Series Size I Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-5FPX-*-R (YELLOW) MIN-5FPX-*-R-B (BLACK)	PVC AWM 5 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	 7/8"-16UN2
	MINP-5FPX-*-R	Yellow PUR AWM 5 X 18 AWG 300V, 5.5A -40°C to +80°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MIN-5FPX-*A-R (YELLOW) MIN-5FPX-*A-R-B (BLACK)	Yellow PVC AWM 5 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	North American Auto Color Code 1. Red/White 2. Red 3. Green/Yellow 4. Red/Yellow 5. Red/Black	
	MINE-5FPX-**R	Yellow PVC AWM 5 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	European 1. Black 2. Blue 3. Green/Yellow 4. Brown 5. White	 7/8"-16UN2
	MIN-6FPX-*-R	Yellow PVC SJTOOW 6 X 18 AWG 300V, 5.5A -40°C to +105°C 10.1mm OD	Industry Standard PVC	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black 6. Blue	 7/8"-16UN2
	MINP-6FPX-*-R	Yellow PUR AWM 6 X 18 AWG 300V, 5.5A -40°C to +80°C 8.5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MINE-6FPX-**R	Yellow PVC SJTOOW 6 X 18 AWG 300V, 5.5A -40°C to +105°C 10.1mm OD	Industry Standard PVC	European 1. Green 2. White 3. Blue 4. Gray 5. Yellow 6. Brown	 7/8"-16UN2

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MIN-5FPX-3-R becomes MIN-5FPX-3-R-SS)

See Page A-33 for Armored Cordset options.