



7/8" MIN Series Size I Cordsets

2, 3 & 4 Conductor MIN Series Size I Cordsets, 16AWG



Right Angle Male Cordsets | 600 Volt, 13 amps | 600 Volt 10 amps | IP67 Rating

A

MIN Series Size I Cordsets



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-2MP-*-R	Yellow PVC STOOW 2 X 16 AWG 600V, 13A -40°C to +105°C 9.5mm OD	Industry Standard PVC	North American 1. White 2. Black	 7/8"-16UN2
	MIN-3MP-*-R (YELLOW) MIN-3MP-*-R-B (BLACK)	PVC STOOW 3 X 16 AWG 600V, 13A -40°C to +105°C 10mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
MINM-3MP-*-R	Yellow PVC STOOW With Foil Shield 3 X 16 AWG 600V, 13A -40°C to +105°C 10mm OD	Industry Standard PVC Foil Shield			
MINP-3MP-*-R	Yellow PUR AWM 3 X 16 AWG 600V, 13A -40°C to +80°C 10mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR			
MINW-3MP-*-R (YELLOW) MINW-3MP-*-B-R (BLACK)	TPE SEOOW 3 X 16 AWG 600V, 13A -40°C to +80°C 10mm OD	Weld Slag Resistant TPE			
MIN-3MP-*-A-R	Yellow PVC STOOW 3 X 16 AWG 600V, 13A -40°C to +105°C 10mm OD	Industry Standard PVC	North American Auto Color Code 1. Green/Yellow 2. Red/Black 3. Red/White		
	MIN-4MP-*-R (YELLOW) MIN-4MP-*-R-B (BLACK)	PVC STOOW 4 X 16 AWG 600V, 10A -40°C to +105°C 10.8mm OD	Industry Standard PVC		
	MINM-4MP-*-R	Yellow PVC STOOW With Foil Shield 4 X 16 AWG 600V, 10A -40°C to +105°C 10.8mm OD	Industry Standard PVC Foil Shield		

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-4MP-3-R becomes MIN-4MP-3-R-SS)

For male threaded coupling replace "MP" with "MPM". (e.g. MIN-3MP-3-R becomes MIN-3MPM-3-R)

See Page A-33 for Armored Cordset options.