



# 7/8" MIN Series Size I Cordsets

5 & 6 Conductor MIN Series Size I Cordsets, 16AWG



Right Angle Male Cordsets | 600 Volt, 8 amps | IP67 Rating

A

MIN Series Size I Cordsets



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-5MP-*-R (YELLOW)  MIN-5MP-*-R-B (BLACK)	PVC STOOW <b>5 X 16 AWG</b> 600V, 8A -40°C to +105°C 13.1mm OD	Industry Standard PVC	<b>North American</b> 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	 7/8"-16UN2
	MINM-5MP-*-R	Yellow PVC STOOW With Foil Shield <b>5 X 16 AWG</b> 600V, 8A -40°C to +105°C 13.1mm OD	Industry Standard PVC Foil Shield		
	MINW-5MP-*-R	Yellow TPE SEOOW <b>5 X 16 AWG</b> 600V, 8A -40°C to +80°C 13.1mm OD	Weld Slag Resistant TPE		
	MIN-5MP-*-A-R	Yellow PVC STOOW <b>5 X 16 AWG</b> 600V, 8A -40°C to +105°C 13.1mm OD	Industry Standard PVC	<b>North American Auto Color Code</b> 1. Red/White 2. Red 3. Green/Yellow 4. Red/Yellow 5. Red/Black	
	MIN-6MP-*-R (YELLOW)  MIN-6MP-*-R-B (BLACK)	PVC STOOW <b>6 X 16 AWG</b> 600V, 8A -40°C to +105°C 13.3mm OD	Industry Standard PVC	<b>North American</b> 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black 6. Blue	 7/8"-16UN2

\* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-6MP-3 becomes MIN-6MP-3-R-SS)

For male threaded coupling replace "MP" with "MPM". (e.g. MIN-5MP-3-R becomes MIN-5MPM-3-R)

See Page A-33 for Armored Cordset options.