



7/8" MIN Series Size I Cordsets

5 & 6 Conductor MIN Series Size I Cordsets, 16AWG



Right Angle Female Cordsets | 600 Volt, 8 amps | IP67 Rating



A

MIN Series Size I Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-5FP-*-R (YELLOW) MIN-5FP-*-R-B (BLACK)	PVC STOOW 5 X 16 AWG 600V, 8A -40°C to +105°C 13.1mm OD	Industry Standard PVC	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	 7/8"-16UN2
	MINM-5FP-*-R	Yellow PVC STOOW With Foil Shield 5 X 16 AWG 600V, 8A -40°C to +105°C 13.1mm OD	Industry Standard PVC Foil Shield		
	MINW-5FP-*-R	Yellow TPE SEOWW 5 X 16 AWG 600V, 8A -40°C to +80°C 13.1mm OD	Weld Slag Resistant TPE		
	MIN-5FP-*-A-R	Yellow PVC STOOW 5 X 16 AWG 600V, 8A -40°C to +105°C 13.1mm OD	Industry Standard PVC		
	MIN-6FP-*-R (YELLOW) MIN-6FP-*-R-B (BLACK)	PVC STOOW 6 X 16 AWG 600V, 8A -40°C to +105°C 13.3mm OD	Industry Standard PVC	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black 6. Blue	 7/8"-16UN2

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-6FP-3-R becomes MIN-6FP-3-R-SS)

See Page A-33 for Armored Cordset options.