



# 7/8" MIN Series Size I Cordsets

3 Conductor MIN Series Size I Cordsets, 18AWG



Straight Female Cordsets | 300 Volt, 8 amps | IP67 Rating



A

MIN Series Size I Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-3FPX-* (YELLOW)  MIN-3FPX-*-B (BLACK)	PVC SJTOOW <b>3 X 18 AWG</b> 300V, 8A -40°C to +105°C 8.5mm OD	Industry Standard PVC	<b>North American</b> 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MIN-3FPX-*A	Yellow PVC SJTOOW <b>3 X 18 AWG</b> 300V, 8A -40°C to +105°C 8.5mm OD	Industry Standard PVC	<b>North American Auto Color Code</b> 1. Green/Yellow 2. Red/Black 3. Red/White	 7/8"-16UN2
	MINE-3FPX-** (YELLOW)  MINE-3FPX-**-B (BLACK)	PVC AWM <b>3 X 18 AWG</b> 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC	<b>European</b> 1. Green/Yellow 2. Brown 3. Blue	 7/8"-16UN2
	MINC-3FPX-**	Yellow PVC AWM <b>3 X 18 AWG</b> 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC	<b>European Cenelec</b> 1. Black 2. Brown 3. Blue	

\* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

\*\* Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-4FPX-3 becomes MIN-3FPX-3-SS)

See Page A-33 for Armored Cordset options.