


## RECEPTACLE, PANEL MOUNTED

|                      |                                                                                                          |
|----------------------|----------------------------------------------------------------------------------------------------------|
| <b>Part No.</b>      | ME 530R9W                                                                                                |
| <b>Description:</b>  | 30 Amp 3 Y 120/208Vac 4 Pole, 5 Wire Receptacle                                                          |
| <b>Construction:</b> | Watertight IEC IP 67                                                                                     |
| <b>Approvals:</b>    | UL Listed Standards 1682; 1686<br>CSA Certification to Spec. C22.2 No. 182.1<br>IEC 60309-1; IEC 60309-2 |

**IEC COLOR CODE:** Blue

**GROUND SOCKET:** 9 Hour Position Mates with Male in 3 Hour Position.



**Wire Range: #8-#12 AWG**

Drawing Not to Scale