



ELECTRONIC/GLASS FUSES



SMG / SMG-V

Glass Body
Fast Acting
5 x 15mm 2AG
1-1/2" Axial Leads Optional

1/10A & 3/8A, 250VAC, UL Listed CSA Certified
1/8A through 7A, 350VAC, UL and CSA Recognized
8A & 10A, 125VAC



STG / STG-V

Glass Body
Time Delay
5 x 15mm 2AG
1-1/2" Axial Leads Optional

3/8A 250VAC, UL Listed and CSA Certified
1/4A through 7A, 350VAC, UL and CSA Recognized

C

Standard Fuse Ampere Ratings

CATALOG NUMBER	AXIAL LEAD CAT. NO	AMPERE RATING	VOLTS	I.R.
SMG1/10	SMG-V1/10	1/10A	250V	1
SMG1/8	SMG-V1/8	1/8A	350V	2
SMG1/4	SMG-V1/4	1/4A	350V	2
SMG3/8	SMG-V3/8	3/8A	250V	1
SMG1/2	SMG-V1/2	1/2A	350V	2
SMG3/4	SMG-V3/4	3/4A	350V	2
SMG1	SMG-V1	1A	350V	2
SMG1-1/2	SMG-V1-1/2	1-1/2A	350V	2
SMG2	SMG-V2	2A	350V	2
SMG2-1/2	SMG-V2-1/2	2-1/2A	350V	2
SMG3	SMG-V3	3A	350V	2
SMG3-1/2	SMG-V3-1/2	3-1/2A	350V	2
SMG4	SMG-V4	4A	350V	2
SMG5	SMG-V5	5A	350V	2
SMG6	SMG-V6	6A	350V	2
SMG7	SMG-V7	7A	350V	2
SMG8	SMG-V8	8A	125V	3
SMG10	SMG-V10	10A	125V	3

1. 250VAC @ 35A I.R./125VAC @ 10kA I.R.
2. 350VAC @ 100A I.R./140VDC @ 150A I.R.
3. 125VAC @ 10kA I.R.

Standard Fuse Ampere Ratings

CATALOG NUMBER	AXIAL LEAD CAT. NO	AMPERE RATING	VOLTS	I.R.
STG1/4	STG-V1/4	1/4A	350V	2
STG3/8	STG-V3/8	3/8A	250V	1
STG1/2	STG-V1/2	1/2A	350V	2
STG6/10	STG-V6/10	6/10A	350V	2
STG3/4	STG-V3/4	3/4A	350V	2
STG8/10	STG-V8/10	8/10A	350V	2
STG1	STG-V1	1A	350V	2
STG1-1/4	STG-V1-1/4	1-1/4A	350V	2
STG1-1/2	STG-V1-1/2	1-1/2A	350V	2
STG2	STG-V2	2A	350V	2
STG2-1/2	STG-V2-1/2	2-1/2A	350V	2
STG3	STG-V3	3A	350V	2
STG3-1/2	STG-V3-1/2	3-1/2A	350V	2
STG4	STG-V4	4A	350V	2
STG5	STG-V5	5A	350V	2
STG6	STG-V6	6A	350V	2
STG7	STG-V7	7A	350V	2

1. 250VAC @ 35A I.R./125VAC @ 10kA I.R.
2. 350VAC @ 100A I.R./125VAC @ 10kA I.R.
3. 1140V DC @ 150A I.R.