

| KVA | CATALOG NUMBER | TAPS FCAN | TAPS FCBN | DESIGN TYPE | TEMP RISE °C | H | W | D | WEIGHT LBS | FRAME NUMBER | WIRING DIAGRAM | WEATHER SHIELD |
|--|----------------|-----------|-----------|-------------|--------------|-------|-------|-------|------------|--------------|----------------|----------------|
| GROUP "I": PRI: 240Δ SEC: 208Y/120 60HZ DOE 2016 | | | | | | | | | | | | |
| 9 | G009K3JH8A03 | - | 4 | 3E | 115 | 15.90 | 16.93 | 10.00 | 190 | 103 | AA | |
| 15 | G015K3JH8A03 | - | 4 | 3E | 115 | 17.38 | 20.00 | 10.50 | 275 | 95 | AA | |
| 30 | G030K3JH2A03 | 6 | 6 | 3E | 115 | 26.58 | 21.81 | 11.65 | 422 | 243 | BB | |
| 45 | G045K3JH2A03 | 6 | 6 | 3E | 115 | 26.58 | 24.81 | 13.53 | 660 | 244 | BB | |
| 15 | G015K5JH2A04 | 6 | 6 | 3V | 150 | 28.00 | 21.88 | 17.75 | 124* | 939 | 280C | WS57MI |
| 30 | G030K5JH2A04 | 6 | 6 | 3V | 150 | 36.88 | 24.88 | 21.13 | 295 | 940 | 280C | WS58MI |
| 45 | G045K5JH2A04 | 6 | 6 | 3V | 150 | 36.88 | 24.88 | 21.13 | 324 | 940 | 280C | WS58MI |
| 75 | G075K5JH2A04 | 6 | 6 | 3V | 150 | 43.00 | 30.50 | 24.00 | 447 | 942 | 280C | WS59MI |
| 112.5 | G112K5JH2A04 | 6 | 6 | 3V | 150 | 51.00 | 34.50 | 31.50 | 760* | 943 | 280C | WS60MI |
| 150 | G150K5JH2A04 | 6 | 6 | 3V | 150 | 51.00 | 34.50 | 31.50 | 974* | 943 | 280C | WS60MI |
| 225 | G225K5JH5A04 | 7 | 7 | 3V | 150 | 60.00 | 38.00 | 33.50 | 1460* | 944 | DD | WS61MI |
| 300 | G300K5JH5A04 | 7 | 7 | 3V | 150 | 66.18 | 42.18 | 33.50 | 1650* | 945 | DD | WS62MI |

(4) 2@ -5%, (6) 2@ +2.5%; 4@ -2.5%, (7) 1@ +5%; 2@ -5%

* EST